

TECHNICAL DATA SHEET

Part No. 151-04084
Article No. 151-04084
Type LOC10-14FT6LG



HellermannTyton's Locking Clamp is ideal for fastening wire and cable bundles to panels. Its uniquely engineered fir tree holds tightly in pre-stamped 6.5 mm holes. The locking clamp mechanism dynamically fits various bundle sizes, while an integrated cable tie saddle allows installers to add additional cable runs. It is easy to install and operate with a single hand and does not require tools, saving time and labor costs.

Material	Polyamide 612 (PA612)
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	2000
Carton Qty.	2000
Customs Number	3926909988

Depth (imperial)	0.47 "
Depth (metric)	12.0 mm
Height (imperial)	2.27 "
Height (metric)	57.75 mm
Max. Bundle Diameter (imperial)	0.55 "
Max. Bundle Diameter (metric)	14.0 mm
Min. Bundle Diameter (imperial)	0.39 "
Min. Bundle Diameter (metric)	10.0 mm
Mounting Hole Diameter (imperial)	0.24 - 0.26 " (HEXAGONAL), 0.24 - 0.28 "
Mounting Hole Diameter (metric)	6.1 - 6.6 mm (hexagonal), 6.1 - 7.0 mm
Panel Thickness (imperial)	0.02 - 0.32 "
Panel Thickness (metric)	0.6 - 8.25 mm
Width (imperial)	0.47 "
Width (metric)	12.0 mm

