

TECHNICAL DATA SHEET

Part No. 151-04085
Article No. 151-04085
Type LOC1014FT9x12



HellermannTyton's Locking Clamp is ideal for fastening wire and cable bundles to panels. Its uniquely engineered fir tree holds tightly in pre-stamped hole sizes from 9x12 mm to 9x14 mm. The locking clamp mechanism dynamically fits various bundle sizes, while an integrated cable tie saddle allows installers to add additional cable runs. It is easy to install and operate with a single hand and does not require tools, saving time and labor costs.

Material	Polyamide 612 (PA612)
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	500
Customs Number	3926909988

Depth (imperial)	0.47 "
Depth (metric)	12.0 mm
Height (imperial)	2.31 "
Height (metric)	58.57 mm
Max. Bundle Diameter (imperial)	0.55 "
Max. Bundle Diameter (metric)	14.0 mm
Min. Bundle Diameter (imperial)	0.39 "
Min. Bundle Diameter (metric)	10.0 mm
Mounting Hole Diameter (imperial)	0.35 x 0.55 ", 0.35 x 0.47 "
Mounting Hole Diameter (metric)	9.0 x 12.0 mm, 9.0 x 14.0 mm
Panel Thickness (imperial)	0.02 - 0.27 "
Panel Thickness (metric)	0.6 - 6.75 mm
Width (imperial)	0.47 "
Width (metric)	12.0 mm

