

TECHNICAL DATA SHEET

Part No. 151-04302
Article No. 151-04302
Type CTCM6CZF



Part of our sustainable line of products, the ReSource product family features solutions made from post-industrial recycled material. It is impact resistant and heat stabilized for a range of operation environments and applications. This cradle mount with frame attachment can be twisted into industrial frames with a 0.7 x 0.31" frame mount and is ideal for routing wires in industrial applications where rework and adjustments are common. Mount features a 0.24" cradle opening for cable retention. The cradle arms can temporarily hold wires for simple adjustments and cable additions and protect against abrasion and cable damage. To permanently mount the bundle, the EZ Feed cable tie slot eliminates common obstructions for faster completion. During rework, the CutZone prevents wire damage when cutting off cable ties.

Height (imperial)	0.55 "
Height (metric)	14.0 mm
Length (imperial)	1.0 "
Length (metric)	25.4 mm
Panel Thickness (imperial)	0.31 "
Panel Thickness (metric)	8.0 mm
Width (imperial)	0.76 "
Width (metric)	19.3 mm
Width 2 (imperial)	0.32 "
Width 2 (metric)	8.0 mm

Material	Polyamide 6.6 recycled, high impact modified, heat stabilized (PA66HIRHS(REC))
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	2000 Pieces
Customs Number	3926909988

