

TECHNICAL DATA SHEET

Part No. 151-04350
Article No. 151-04350
Type ROC18.5-22.5CLIP17



The Ratchet O-Clamp is designed for tight spaces, maintaining a low profile while providing an adjustable closure for a range of bundle sizes. HellermannTyton's connector clips provide a single method to mount connectors to various surfaces in a variety of applications. Clips can be paired with brackets for custom routing needs.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	1000 Pieces
Customs Number	3926909988

Connection Type	USCAR17
Fixation Method	Connector Clip
Length (imperial)	2.29 "
Length (metric)	58.1 mm
Max. Bundle Diameter (imperial)	0.88 "
Max. Bundle Diameter (metric)	22.5 mm
Min. Bundle Diameter (imperial)	0.73 "
Min. Bundle Diameter (metric)	18.5 mm
Min. Tensile Strength (imperial)	100 lbs
Min. Tensile Strength (metric)	445 N
Width (imperial)	0.81 "
Width (metric)	20.5 mm

