

TECHNICAL DATA SHEET

Part No. 151-04352
Article No. 151-04352
Type ROC18.5-22.5FTOVAL



The Ratchet O-Clamp is designed for tight spaces, maintaining a low profile while providing an adjustable closure for a range of bundle sizes. It is designed for fluid routing and high-voltage cable management. An integrated fir tree provides a secure grip into oval mounting holes with no additional hardware.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	1000 Pieces
Customs Number	3926909988

Fixation Method	Fir Tree
Length (imperial)	2.29 "
Length (metric)	58.1 mm
Max. Bundle Diameter (imperial)	0.88 "
Max. Bundle Diameter (metric)	22.5 mm
Min. Bundle Diameter (imperial)	0.73 "
Min. Bundle Diameter (metric)	18.5 mm
Min. Tensile Strength (imperial)	100 lbs
Min. Tensile Strength (metric)	445 N
Mounting Hole Diameter (imperial)	0.24 x 0.48 ", 0.26 x 0.49 ", 0.26 x 0.51 ", 0.28 x 0.47 "
Mounting Hole Diameter (metric)	6.2 x 12.2 mm, 6.5 x 12.5 mm, 6.5 x 13.0 mm, 7.0 x 12.0 mm
Panel Thickness (imperial)	0.02 - 0.27 "
Panel Thickness (metric)	0.6-6.75 mm
Width (imperial)	0.81 "
Width (metric)	20.5 mm

