

TECHNICAL DATA SHEET

Part No. 151-04425
Article No. 151-04425
Type SPC-DEC1-3SP



Designed to securely hold an MC4, MC4 EVO2 or comparable solar connector with an outer diameter of 21.5 mm and a maximum length of 122.0 mm. The solar connector can be easily fitted and removed at any time.

Material	Polyamide 6.6 heat and UV stabilized (PA66HSUV), Steel C75S (C75S)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	60
Carton Qty.	480
Customs Number	3926909988

Fixation Method	EdgeClip, sideways
Height (imperial)	1.02 "
Height (metric)	26.0 mm
Length (imperial)	6.39 "
Length (metric)	162.4 mm
Panel Thickness (imperial)	0.04 - 0.12 "
Panel Thickness (metric)	1.0 - 3.0 mm
Width (imperial)	1.26 "
Width (metric)	31.9 mm

