

TECHNICAL DATA SHEET

Part No. 151-04487
Article No. 151-04487
Type CTSM3CZS



Designed specifically for holding heavier cable bundles, these mounting bases can be used in many industries from agriculture to truck manufacturing. They mount securely and can be used with a wide variety of heavy duty cable ties up to 8.3 mm in width. Cables are held in place and aligned by troughs in the mount's arms. The EZ Feed cable tie slot eliminates common obstructions for faster completion. During rework, the CutZone prevents wire damage when cutting off cable ties.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	White (WH)
Pkg. Qty.	1000
Carton Qty.	3000
Customs Number	3926909988

Fixation Method	Screw Mounting and Rivet
Height (imperial)	0.46 "
Height (metric)	11.7 mm
Length (imperial)	1.1 "
Length (metric)	28.0 mm
Max. Cable Tie Width (imperial)	0.33 "
Max. Cable Tie Width (metric)	8.4 mm
Mounting Hole Diameter (imperial)	0.21 "
Mounting Hole Diameter (metric)	5.35 mm
Mounting Screw Type	#10 (M5) Screw
Width (imperial)	0.66 "
Width (metric)	16.8 mm

HF ✓

RoHS ✓