TECHNICAL DATA SHEET

HellermannTyton

Part No. 151-04574
Article No. 151-04574
Type WRMB12AHB



The WireRail routing aid combines heavy duty strength and adhesion with high aesthetics and versatility. The 12-inch-long footprint creates perfectly straight vertical or horizontal cable routings. Eight cable tie slots offer flexibility in anchoring wire runs. Choose from acrylic- or rubber-based adhesive, depending on application and mounting environment. One WireRail can replace three-plus square adhesive mounts, for part and labor savings.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Adhesive	High Bond Acrylic
Operating Temperature	-13°F to +158°F (-25°C to +70°C)
Flammability	UL 94 V-2 (excluding adhesive)
Halogen Free	No
UV Resistant	Yes
Use Conditions	For Indoor Use Only
Color	Black (BK)

Pkg. Qty.	300
Carton Qty.	300
Customs Number	3926909988

Fixation Method	Screw Mounting and Adhesive
For Cable Tie Series	T18 - T120; GT.375 - GT.75
Height (imperial)	0.33 "
Height (metric)	8.5 mm
Length (imperial)	12.0 "
Length (metric)	304.8 mm
Width (imperial)	0.86 "
Width (metric)	21.9 mm

RoHS

Contact HellermannTyton for more information. Visit www.hellermann.tyton.com or call 800.537.1512
Disclaimer: The information in this datasheet is for informational purposes only.
Information is subject to change at any time without notice.

created on 2026-06-30