

TECHNICAL DATA SHEET

Part No. 151-04619
Article No. 151-04619
Type CTCM11CZA-AE



This cradle mount with acrylic adhesive is fast and easy to apply to any flat surface and is ideal for routing wires in industrial applications where rework and adjustments are common. Mount features a 0.43" cradle opening enhanced with retention arms, providing temporary cable management for simple adjustments and cable additions, or final cable attachment with near-zero chance of disengagement. Cradle also protects against abrasion and cable damage. To permanently mount the bundle, the EZ Feed cable tie slot eliminates common obstructions for faster completion. During rework, the CutZone prevents wire damage when cutting off cable ties.

Fixation Method	Screw Mounting and Adhesive
For Cable Tie Series	T18 - T120;GT.375
Height (imperial)	0.79 "
Height (metric)	20.1 mm
Length (imperial)	1.23 "
Length (metric)	31.2 mm
Width (imperial)	0.93 "
Width (metric)	23.73 mm

Material	Polyamide 6.6 heat stabilized (PA66HS)
Adhesive	High Bond Acrylic
Operating Temperature	-13°F to +158°F (-25°C to +70°C)
Flammability	UL 94 V-2 (excluding adhesive)
Halogen Free	No
UV Resistant	Yes
Use Conditions	For Indoor Use Only
Color	Black (BK)

Pkg. Qty.	100
Carton Qty.	2000
Customs Number	3926909988

RoHS

