

TECHNICAL DATA SHEET

Part No. 151-04647
Article No. 151-04647
Type ROC18.5-22.5ATI2



The Ratchet O-Clamp for Array Technologies attaches easily to ATI torque tubes thanks to a custom-designed clip. It offers one-handed, toolless simplicity and size versatility for managing wires and cables on solar modules. The robust design and solar-optimized materials make it ideal for heavy duty, outdoor applications. The one-piece adjustable clamp can be closed by hand to the desired diameter, replacing multiple sizes for single-diameter fasteners.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV), Stainless Steel (SS304)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	200
Carton Qty.	200 Pieces
Customs Number	3926909988

Fixation Method	Connector Clip
Length (imperial)	1.5 "
Length (metric)	37 mm
Max. Bundle Diameter (imperial)	0.89 "
Max. Bundle Diameter (metric)	22.5 mm
Min. Bundle Diameter (imperial)	0.73 "
Min. Bundle Diameter (metric)	18.5 mm
Min. Tensile Strength (imperial)	100 lbs
Min. Tensile Strength (metric)	445 N
Panel Thickness (imperial)	0.16 "
Panel Thickness (metric)	4.0 mm
Width (imperial)	1.7 "
Width (metric)	42.5 mm

