

# TECHNICAL DATA SHEET

**Part No.** 151-04681  
**Article No.** 151-04681  
**Type** AMB6AHB



The HellermannTyton Anchor Mount is specially designed for areas that see excessive movement, stress or tension, particularly around hinges or corners. It provides heavy duty strength and adhesion with its extra-large surface area and high-bond acrylic adhesive. The radius guide helps hold and guide bundles up and around hinges, corners, or other obstructions. The mount features a retention arm to help hold wires in place during the planning phases of cable installations, allowing for rework if needed.

<b>Fixation Method</b>	Screw Mounting and Adhesive
<b>For Cable Tie Series</b>	T18-T120;GT.375
<b>Height (imperial)</b>	1.1 "
<b>Height (metric)</b>	27.2 mm
<b>Length (imperial)</b>	2.4 "
<b>Length (metric)</b>	62.0 mm
<b>Width (imperial)</b>	2.4 "
<b>Width (metric)</b>	62.0 mm

<b>Material</b>	Polyamide 6.6 heat stabilized (PA66HS)
<b>Adhesive</b>	High Bond Acrylic
<b>Operating Temperature</b>	-13°F to +158°F (-25°C to +70°C)
<b>Flammability</b>	UL 94 V-2 (excluding adhesive)
<b>Halogen Free</b>	No
<b>UV Resistant</b>	No
<b>Use Conditions</b>	For Indoor Use Only
<b>Color</b>	White (WH)

<b>Pkg. Qty.</b>	50
<b>Carton Qty.</b>	500
<b>Customs Number</b>	3926909988

