

TECHNICAL DATA SHEET

Part No. 151-04683
Article No. 151-04683
Type WRMB12A



The WireRail routing aid combines heavy duty strength and adhesion with high aesthetics and versatility. The 12-inch-long footprint creates perfectly straight vertical or horizontal cable routings. Eight cable tie slots offer flexibility in anchoring wire runs. Choose from acrylic- or rubber-based adhesive, depending on application and mounting environment. One WireRail can replace three-plus square adhesive mounts, for part and labor savings.

Material	Polyamide 6.6 heat stabilized (PA66HS)
Adhesive	Synthetic rubber with base of polyethylene foam
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2 (excluding adhesive)
Halogen Free	No
Use Conditions	For Indoor Use Only
Color	White (WH)
Pkg. Qty.	50
Carton Qty.	300
Customs Number	3926909988

Fixation Method	Screw Mounting and Adhesive
For Cable Tie Series	T18 - T120; GT.375 - GT.75
Height (imperial)	0.33 "
Height (metric)	8.5 mm
Length (imperial)	12.0 "
Length (metric)	304.8 mm
Width (imperial)	0.86 "
Width (metric)	21.9 mm

RoHS ✓