

TECHNICAL DATA SHEET

Part No. 151-10916
Article No. 151-10916
Type QM40A



Q Mounts are designed to work exclusively with the Q Tie cable tie series. This mounting component is available with adhesive or can be secured with screws. The Q Mount allows either a 2- or 4-way entry for the Q Tie, providing a quick and simple insertion into the mount. Once in place, the Q Tie will not slip out, even in vertical mounting applications.

Material	Polyamide 6.6 (PA66)
Adhesive	Synthetic rubber with base of polyethylene foam
Operating Temperature	-40°F to +140°F (-40°C to +60°C)
Flammability	UL 94 V-2 (excluding adhesive)
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	50
Carton Qty.	1000
Customs Number	3926909988

Fixation Method	Adhesive
Height (imperial)	0.26 "
Height (metric)	5.5 mm
Length (imperial)	1.6 "
Length (metric)	40.0 mm
Width (imperial)	1.6 "
Width (metric)	40.0 mm

