

TECHNICAL DATA SHEET

Part No. 151-10930
Article No. 151-10930
Type CTQM5



Q-Series mounting bases are designed to work exclusively with the Q-Tie® cable tie series. This mounting component can be secured with screws. The Q-Mount allows either a two- or four-way entry for the Q-Tie, providing a quick and simple insertion into the mount. Once in place, the Q-Tie will not slip out, even in vertical mounting applications.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	3000
Customs Number	3926909988

Fixation Method	Screw Mount
For Cable Tie Series	Q-Ties
Height (imperial)	0.26 "
Height (metric)	6.7 mm
Length (imperial)	0.83 "
Length (metric)	21.0 mm
Max. Cable Tie Width (imperial)	0.2 "
Max. Cable Tie Width (metric)	5.0 mm
Mounting Hole Diameter (imperial)	0.175 "
Mounting Hole Diameter (metric)	4.5 mm
Mounting Screw Type	M4 Screw
Width (imperial)	0.38 "
Width (metric)	9.5 mm

