

TECHNICAL DATA SHEET

Part No. RB8L4
Article No. 151-13608
Type RB8



The RB Adhesive cable clamps are designed with an easy snap-in feature allowing simple installation or removal of cables, pipes or hoses. The rubber based adhesive allows for a permanent bond to most surfaces.

Material	Polyamide 6.6 (PA66)
Adhesive	Synthetic rubber with base of polyethylene foam
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2 (excluding adhesive)
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	200
Carton Qty.	4000
Customs Number	3926909988

Fixation Method	Pasting / Stick
Height (imperial)	0.45 "
Height (metric)	11.5 mm
Length (imperial)	0.98 "
Length (metric)	25.0 mm
Max. Bundle Diameter (imperial)	0.31 "
Max. Bundle Diameter (metric)	8.0 mm
Min. Bundle Diameter (imperial)	0 "
Width (imperial)	1.0 "
Width (metric)	25.0 mm

RoHS✓