

TECHNICAL DATA SHEET

Part No. MB50F4
Article No. 151-28501
Type MB5



These cable tie mounts are compact in size. They are designed for simple yet robust installation. They pair with a cable tie for mounting applications including telecom equipment, switchgear and control cabinets.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	250
Carton Qty.	3000
Customs Number	3926909988

Fixation Method	Screw Mount
For Cable Tie Series	T18 - T150
Height (imperial)	.25 "
Height (metric)	6.20 mm
Length (imperial)	1.49 "
Length (metric)	37.7 mm
Max. Cable Tie Width (imperial)	0.35 "
Max. Cable Tie Width (metric)	8.9 mm
Mounting Hole Diameter (imperial)	0.19 "
Mounting Hole Diameter (metric)	4.8 mm
Mounting Screw Type	#8 Screw
Width (imperial)	1.49 "
Width (metric)	37.7 mm

RoHS

