

# TECHNICAL DATA SHEET

**Part No.** MB5A10A2F4  
**Article No.** 151-28610  
**Type** MB5A



HellermannTyton adhesive fastened mounting bases are used with 18 through 150 pound cable ties to provide stability when securing bundles. The mounts are installed using the adhesive backing and/or by securing two or four screws. The 4 way opening allows the cable ties to be inserted parallel or perpendicular to the wire bundles.

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Adhesive</b>	Acrylate with base of polyethylene foam
<b>Operating Temperature</b>	-40°F to +185°F (-40°C to +85°C)
<b>Flammability</b>	UL 94 V-2 (excluding adhesive)
<b>UV Resistant</b>	No
<b>Use Conditions</b>	For Indoor Use Only
<b>Color</b>	White (WH)
<b>Pkg. Qty.</b>	250
<b>Carton Qty.</b>	2000
<b>Customs Number</b>	3926909988

<b>Fixation Method</b>	Adhesive
<b>For Cable Tie Series</b>	T18 - T150
<b>Height (imperial)</b>	.28 "
<b>Height (metric)</b>	7.1 mm
<b>Length (imperial)</b>	1.49 "
<b>Length (metric)</b>	37.7 mm
<b>Max. Static Load (imperial)</b>	2.1 lbf-ft
<b>Maximum Static Load (N)</b>	9.341 N
<b>Width (imperial)</b>	1.49 "
<b>Width (metric)</b>	37.7 mm

