

TECHNICAL DATA SHEET

Part No. MB40H4
Article No. 151-28801
Type MB4



These cable tie mounts are compact in size. They are designed for simple yet robust installation. They pair with a cable tie for mounting applications including telecom equipment, switchgear and control cabinets.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	5000
Customs Number	3926909988

Fixation Method	Screw Mount
For Cable Tie Series	T18 - T50
Height (imperial)	.19 "
Height (metric)	4.80 mm
Length (imperial)	1.12 "
Length (metric)	28.5 mm
Max. Cable Tie Width (imperial)	0.18 "
Max. Cable Tie Width (metric)	4.6 mm
Mounting Hole Diameter (imperial)	0.18 "
Mounting Hole Diameter (metric)	4.6 mm
Mounting Screw Type	#8 Screw
Width (imperial)	1.12 "
Width (metric)	28.5 mm

RoHS 

