

TECHNICAL DATA SHEET

Part No. MB2.510C2
Article No. 151-28901
Type MB2.5



These cable tie mounts are compact in size. They are designed for simple yet robust installation. They pair with a cable tie for mounting applications including telecom equipment, switchgear and control cabinets.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	White (WH)
Pkg. Qty.	100
Carton Qty.	15000
Customs Number	3926909988

Fixation Method	Screw Mount
For Cable Tie Series	T18
Height (imperial)	0.13 "
Height (metric)	3.30 mm
Length (imperial)	0.625 "
Length (metric)	15.9 mm
Max. Cable Tie Width (imperial)	0.1 "
Max. Cable Tie Width (metric)	2.54 mm
Mounting Hole Diameter (imperial)	0.11 "
Mounting Hole Diameter (metric)	2.8 mm
Mounting Screw Type	#3 Screw
Width (imperial)	0.625 "
Width (metric)	15.9 mm

RoHS 

