

TECHNICAL DATA SHEET

Part No. MB4SH10C2
Article No. 151-29104
Type MB4SH



These cable tie mounts are compact in size. They are designed for simple yet robust installation. They pair with a cable tie for mounting applications including telecom equipment, switchgear and control cabinets.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	White (WH)
Pkg. Qty.	100
Carton Qty.	5000
Customs Number	3926909988

Fixation Method	Screw Mount
For Cable Tie Series	T18 - T50
Height (imperial)	.20 "
Height (metric)	5.10 mm
Length (imperial)	1.12 "
Length (metric)	28.3 mm
Max. Cable Tie Width (imperial)	0.18 "
Max. Cable Tie Width (metric)	4.6 mm
Mounting Hole Diameter (imperial)	0.15 "
Mounting Hole Diameter (metric)	3.9 mm
Mounting Screw Type	#6 Screw
Width (imperial)	1.12 "
Width (metric)	28.3 mm

RoHS

