

TECHNICAL DATA SHEET

Part No. MB4SHA0C2
Article No. 151-29200
Type MB4SHA



MB4SHA adhesive mounts are for use with HellermannTyton T18 - T50 Series cable ties to provide stability when securing bundles. The rubber adhesive-backed mounts can be used to secure a bundle and have a predrilled hole to extend mounting options.

Material	Polyamide 6.6 (PA66)
Adhesive	Synthetic rubber with base of polyethylene foam
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2 (excluding adhesive)
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	4000
Customs Number	3926909988

Fixation Method	Adhesive
For Cable Tie Series	T18 - T50
Height (imperial)	.23 "
Height (metric)	5.8 mm
Length (imperial)	1.12 "
Length (metric)	28.3 mm
Max. Static Load (imperial)	1.1 lbf-ft
Maximum Static Load (N)	4.893 N
Width (imperial)	1.12 "
Width (metric)	28.3 mm

