

# TECHNICAL DATA SHEET

**Part No.** MB4SHA10H4  
**Article No.** 151-29206  
**Type** MB4SHA



MB4SHA adhesive mounts are for use with HellermannTyton T18 - T50 Series cable ties to provide stability when securing bundles. The rubber adhesive-backed mounts can be used to secure a bundle and have a predrilled hole to extend mounting options.

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Adhesive</b>	Synthetic rubber with base of polyethylene foam
<b>Operating Temperature</b>	-40°F to +185°F (-40°C to +85°C)
<b>Flammability</b>	UL 94 V-2 (excluding adhesive)
<b>UV Resistant</b>	No
<b>Use Conditions</b>	For Indoor Use Only
<b>Color</b>	White (WH)
<b>Pkg. Qty.</b>	500
<b>Carton Qty.</b>	4000
<b>Customs Number</b>	3926909988

<b>Adhesive</b>	Synthetic rubber with base of polyethylene foam
<b>Cable Ties</b>	T18 - T50
<b>Fixation Method</b>	Adhesive
<b>Height (imperial)</b>	.23 "
<b>Height (metric)</b>	5.8 mm
<b>Length (imperial)</b>	1.12 "
<b>Length (metric)</b>	28.3 mm
<b>Max. Static Load (imperial)</b>	1.1 lbf-ft
<b>Maximum Static Load (N)</b>	4.893 N
<b>Width (imperial)</b>	1.12 "
<b>Width (metric)</b>	28.3 mm

