

TECHNICAL DATA SHEET

Part No. S3STM500HIRHSF1
Article No. 151-29501
Type S3STM50



The saddle mount acts as a standoff, elevating bundles above bolt protrusions commonly found in frame rails and panels. A tension tab on the mount allows cable ties to be pre-assembled in a ready position prior to bundles being brought to the mount. The mount can secure up to four separate bundles, providing parallel spacing between the frame rail and adjacent bundles. Fir tree eliminates the need for mounting hardware. For use with HellermannTyton T50-T255 ties.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	250
Carton Qty.	250
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Height (imperial)	1.40 "
Height (metric)	35.0 mm
Length (imperial)	2.0 "
Length (metric)	50.0 mm
Max. Bundle Diameter (imperial)	5 "
Max. Bundle Diameter (metric)	127.0 mm
Max. Cable Tie Width (imperial)	0.51 "
Max. Cable Tie Width (metric)	13.0 mm
Min. Bundle Diameter (imperial)	5 "
Min. Bundle Diameter (metric)	127.0 mm
Mounting Hole Diameter (imperial)	0.5 - 0.54 "
Mounting Hole Diameter (metric)	12.7 - 13.7 mm
Panel Thickness (imperial)	0.07 - 0.51 "
Panel Thickness (metric)	1.9 - 13.0 mm
Width (imperial)	1.06 "
Width (metric)	26.9 mm

HF ✓

RoHS ✓