

TECHNICAL DATA SHEET

Part No. CTM09M4
Article No. 151-30307
Type CTMO



Designed specifically for holding heavier cable bundles these mounting bases can be used in many industries from agriculture to truck manufacture. They offer a very secure fixing and can be used with a wide variety of heavy duty cable ties up to 8.3 mm width.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Natural (NA)
Pkg. Qty.	1000
Carton Qty.	15000
Customs Number	3926909988

Fixation Method	Screw Mount
For Cable Tie Series	T18 - T50
Height (imperial)	0.27 "
Height (metric)	6.9 mm
Length (imperial)	0.58 "
Length (metric)	14.7 mm
Max. Cable Tie Width (imperial)	0.2 "
Max. Cable Tie Width (metric)	5.0 mm
Mounting Hole Diameter (imperial)	0.15 "
Mounting Hole Diameter (metric)	3.8 mm
Mounting Screw Type	#6 (M3) Screw
Width (imperial)	0.37 "
Width (metric)	9.4 mm

