

TECHNICAL DATA SHEET

Part No. CTM30C2
Article No. 151-30600
Type CTM3



Designed specifically for holding heavier cable bundles these mounting bases can be used in many industries from agriculture to truck manufacture. They offer a very secure fixing and can be used with a wide variety of heavy duty cable ties up to 8.3 mm width.

Material	Polyamide 6.6 (PA66)
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	5000
Customs Number	3926909988

Fixation Method	Screw Mount
For Cable Tie Series	T18 - T120
Height (imperial)	.37 "
Height (metric)	9.40 mm
Length (imperial)	0.86 "
Length (metric)	21.8 mm
Max. Cable Tie Width (imperial)	0.31 "
Max. Cable Tie Width (metric)	7.9 mm
Mounting Hole Diameter (imperial)	0.2 "
Mounting Hole Diameter (metric)	5.1 mm
Mounting Screw Type	#10 (M5) Screw
Width (imperial)	0.61 "
Width (metric)	15.5 mm

