

TECHNICAL DATA SHEET

Part No. FC1.2AH4
Article No. 154-00012
Type FC1.2A



HellermannTyton's flat ribbon clamps route, protect, and secure flat ribbon cables without damage to sensitive wires and cables. The unique, adjustable height feature allows the clamp to close to the exact height of the ribbon cable, using only as much force as needed to secure the cable. The releasable feature allows simple opening when access to the cable is necessary.

Material	Polyamide 6.6 (PA66)
Adhesive	Acrylate with base of polyurethane foam
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Flammability	UL 94 V-2 (excluding adhesive)
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Gray (GY)
Pkg. Qty.	500
Carton Qty.	2000
Customs Number	3926909988

Height (imperial)	0.5 "
Height (metric)	12.7 mm
Length (imperial)	0.81 "
Length (metric)	20.57 mm
Max Cable Width (metric)	30.48 mm
Max. Cable Width (imperial)	1.2 "
Max. Mounting Hole Diameter (metric)	4.0 mm
Min. Mounting Hole Diameter (metric)	4.0 mm
Mounting Hole Diameter (imperial)	0.157 "
Mounting Hole Diameter (metric)	4.0 mm
Width (imperial)	1.5 "
Width (metric)	38.1 mm
Width 2 (imperial)	0.75 "

