

# TECHNICAL DATA SHEET

**Part No.** 155-01600  
**Article No.** 155-01600  
**Type** STAND-OFF-CLIP-2



Standoff bundling clips provide a straightforward way to secure cable bundles, hoses or pipes. The bundle fastens to the tape bar using tape or cable ties. Multiple orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standoff keeps bundles away from mounting area to prevent them from damage due to rubbing.

|                              |                                                                  |
|------------------------------|------------------------------------------------------------------|
| <b>Material</b>              | Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) |
| <b>Operating Temperature</b> | -40°F to +221°F (-40°C to +105°C)                                |
| <b>Flammability</b>          | UL 94 HB                                                         |
| <b>UV Resistant</b>          | No                                                               |
| <b>Use Conditions</b>        | For Indoor and Outdoor Use                                       |
| <b>Color</b>                 | Black (BK)                                                       |
| <b>Pkg. Qty.</b>             | 500                                                              |
| <b>Carton Qty.</b>           | 6000                                                             |
| <b>Customs Number</b>        | 3926909988                                                       |

|                                          |               |
|------------------------------------------|---------------|
| <b>Fixation Method</b>                   | Arrowhead     |
| <b>Length (imperial)</b>                 | 1.57 "        |
| <b>Length (metric)</b>                   | 40.0 mm       |
| <b>Mounting Hole Diameter (imperial)</b> | 0.26 - 0.27 " |
| <b>Mounting Hole Diameter (metric)</b>   | 6.5 - 6.8 mm  |
| <b>Offset Length (imperial)</b>          | 0.98 "        |
| <b>Offset Length (metric)</b>            | 25.0 mm       |
| <b>Panel Thickness (imperial)</b>        | 0.02 - 0.06 " |
| <b>Panel Thickness (metric)</b>          | 0.4 - 1.6 mm  |
| <b>Tape Bar Length (imperial)</b>        | 1.57 "        |
| <b>Tape Bar Length (metric)</b>          | 40.0 mm       |

RoHS 