

TECHNICAL DATA SHEET

Part No. 155-05400
Article No. 155-05400
Type T50SOSSB5-HIGH-E



The special oval shape provides for an approximate .20" (5.0 mm) lateral adjustment, allowing for any misalignment of the stud or incorrect positioning of the tie on the cables

Material	Polyamide 6.6 heat stabilized (PA66HS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	3000
Customs Number	3926909988

Fixation Method	Stud Mount
Length (imperial)	6.0 "
Length (metric)	160 mm
Max. Bundle Diameter (imperial)	1.38 "
Max. Bundle Diameter (metric)	35.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	170 N
Stud Diameter (imperial)	0.2 "
Stud Diameter (metric)	5.0 mm
Thickness (imperial)	0.05 "
Thickness (metric)	1.35 mm
Width (imperial)	0.19 "
Width (metric)	4.6 mm

