

TECHNICAL DATA SHEET

Part No. 155-05800
Article No. 155-05800
Type T50SOSFT6E



One-piece mounting ties offer a complete solution by both bundling and mounting wires, cables and tubes. The fir tree mount provides low insertion force with a high extraction force. Outside serrations on the cable tie leave a smooth interior surface that's gentler on sensitive wire insulation. The unique head design allows the cable tie to firmly hold bundles as small as .06" diameter. The disc offers added protection against debris.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1500
Carton Qty.	7500
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Height (imperial)	0.33 "
Length (imperial)	6.0 "
Length (metric)	160 mm
Max. Bundle Diameter (imperial)	1.26 "
Max. Bundle Diameter (metric)	32.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	150 N
Mounting Hole Diameter (imperial)	0.26 - 0.28 "
Mounting Hole Diameter (metric)	6.5 - 7.0 mm
Panel Thickness (imperial)	0.03 - 0.12 "
Panel Thickness (metric)	0.75 - 3.0 mm
Thickness (imperial)	0.05 "
Thickness (metric)	1.35 mm
Width (imperial)	0.19 "
Width (metric)	4.7 mm

RoHS ✓