

TECHNICAL DATA SHEET

Part No. 155-30802
Article No. 155-30802
Type TC2FT6LG



HellermannTyton Bundling Clips are designed to provide simple and easy methods for securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using tape or cable ties.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	14000
Carton Qty.	14000
Customs Number	3926909988

Fixation Method	Fir Tree
Height (imperial)	0.49 "
Height (metric)	12.5 mm
Length (imperial)	2.17 "
Length (metric)	55.0 mm
Mounting Hole Diameter (imperial)	0.25 - 0.28 "
Mounting Hole Diameter (metric)	6.3 - 7.0 mm
Panel Thickness (imperial)	0.02 - 0.20 "
Panel Thickness (metric)	0.6 - 5.1 mm
Tape Bar Length (imperial)	2.17 "
Tape Bar Length (metric)	55.0 mm
Width (imperial)	0.355 "
Width (metric)	9.0 mm

HF ✓

RoHS ✓