

TECHNICAL DATA SHEET

Part No. 155-32602
Article No. 155-32602
Type FT6LG.M.St.Aufn.II



Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	15000
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Length (imperial)	1.06 "
Length (metric)	27.0 mm
Mounting Hole Diameter (imperial)	0.26 - 0.28 "
Mounting Hole Diameter (metric)	6.5 - 7.0 mm
Panel Thickness (imperial)	0.03 - 0.20 "
Panel Thickness (metric)	0.75 - 5.0 mm
Width (imperial)	0.63 "
Width (metric)	16.0 mm

