

Technical data sheet

Article number:**156-01293****T50R0GSBS5USET**

Material	Polyamide 6.6, heat stabilised (PA66HS), Polyamide 6.6, high impact modified, heat stabilised (PA66HIRHS)
Colour	Black (BK), Grey (GY)
Bundle Ø max.	50.0 mm
Bundle Ø min.	4.0 mm
CE Certification	No
Fixation Method	Weld Stud Fixing
for Hole Ø (FH)	M5 x 0.8, T5
Height (H)	21.5 mm
Length (L)	203.2 mm
Min.Tensile Strength	110 N
Operating Temperature	-40 °C to +105 °C
Package Content packed in	carton
Pack Cont.	2000 pcs.
ROHS compliant	Yes
Stud Ø	5.0 mm

RoHS 