

Technical data sheet

Article number:
156-01571

T50R0SBL6UM90SET

Material	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV), Polyacetal (POM)
Colour	Black (BK)
Bundle Ø max.	50.0 mm
Bundle Ø min.	1.5 mm
Cable Tie	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
CE Certification	No
Fixation Method	Stud Mount
Flammability	UL 94 HB
for Hole Ø (FH)	M6 x 1
Height (H)	25.0 mm
Length (L)	202.0 mm
Min.Tensile Strength	225 N
Operating Temperature	-40 °C to +105 °C, -30 °C to +90 °C
Package Content packed in	bag
Pack Cont.	2000 pc.
ROHS compliant	Yes
Stud Ø	6.0 mm
Width (W)	11.72 mm

HF ✓

RoHS ✓