

Technical data sheet

Article number:**156-02831****T50SMVCOC10-14**

Product Group	2-piece fixing ties with pipe clip
Material	Polyamide 6.6, high impact modified, heat stabilised (PA66HIRHS), Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
Colour	Black (BK)
Application Tool	ProCut 9 no battery, MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7iSP, EVO9, EVO9SP, EVO9i, EVO9iSP
Bundle Ø max.	50.0 mm
Bundle Ø min.	2.0 mm
CE Certification	No
Fixation Method	Omega Clip
Length (L)	210.0 mm
Min.Tensile Strength	222 N
Operating Temperature	-40 °C to +85 °C
Package Content packed in	bag
Pack Cont.	3000 pcs.
ROHS compliant	Yes
Width (W)	4.7 mm

RoHS ✓