

Technical data sheet

Article number:**156-03181****T120SFT8M10SET**

Material	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
Colour	Black (BK)
Bundle Ø max.	55.0 mm
Bundle Ø min.	5.0 mm
Cable Tie	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
CE Certification	No
Fixation Method	Fir tree for round holes
Flammability	UL 94 HB
for Hole Ø (FH)	8.0 mm
Height (H)	22.77 mm
Length (L)	229.0 mm
Min.Tensile Strength	535 N
Operating Temperature	-40 °C to +105 °C
Package Content packed in	pack
Pack Cont.	1000 pcs.
Panel Thickness	6.0 mm
Panel Thickness max.	0.6 - 6.0 mm
Panel Thickness min. (metric)	0.6 mm
ROHS compliant	Yes
Variant	Inside Serrated
Width (W)	7.6 mm

RoHS 