

# TECHNICAL DATA SHEET

**Part No.** 156-00057  
**Article No.** 156-00057  
**Type** T30RFT7



HellermannTyton's fir tree mounts provide a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. Fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold as an assembly with the cable tie.

|                                        |                                        |
|----------------------------------------|----------------------------------------|
| <b>Material</b>                        | Polyamide 6.6 heat stabilized (PA66HS) |
| <b>Material Cable Tie</b>              | PA66HS                                 |
| <b>Material Foot Part</b>              | PA66HS                                 |
| <b>Operating Temperature</b>           | -40°F to +221°F (-40°C to +105°C)      |
| <b>Foot Part Operating Temperature</b> | -40°F to +221°F (-40°C to +105°C)      |
| <b>Flammability</b>                    | UL 94 V-2                              |
| <b>UV Resistant</b>                    | No                                     |
| <b>Use Conditions</b>                  | For Indoor and Outdoor Use             |
| <b>Color</b>                           | Black (BK)                             |
| <b>Pkg. Qty.</b>                       | 500                                    |
| <b>Carton Qty.</b>                     | 4000                                   |
| <b>Customs Number</b>                  | 3926909988                             |

|                                          |                          |
|------------------------------------------|--------------------------|
| <b>Fixation Method</b>                   | Fir tree for round holes |
| <b>Height (imperial)</b>                 | 0.04 "                   |
| <b>Height (metric)</b>                   | 1.1 mm                   |
| <b>Length (imperial)</b>                 | 6.0 "                    |
| <b>Length (metric)</b>                   | 150.0 mm                 |
| <b>Length 2 (imperial)</b>               | 0.46 "                   |
| <b>Length 2 (metric)</b>                 | 11.6 mm                  |
| <b>Max. Bundle Diameter (imperial)</b>   | 1.38 "                   |
| <b>Max. Bundle Diameter (metric)</b>     | 35.0 mm                  |
| <b>Min. Tensile Strength (imperial)</b>  | 30 lbs                   |
| <b>Min. Tensile Strength (metric)</b>    | 135 N                    |
| <b>Mounting Hole Diameter (imperial)</b> | 0.26 - 0.28 "            |
| <b>Mounting Hole Diameter (metric)</b>   | 6.5 - 7.0 mm             |
| <b>Panel Thickness (imperial)</b>        | 0.03 - 0.28 "            |
| <b>Panel Thickness (metric)</b>          | 0.8 - 7.0 mm             |
| <b>Thickness (metric)</b>                | 1.1 mm                   |
| <b>Width (imperial)</b>                  | 0.14 "                   |
| <b>Width (metric)</b>                    | 3.5 mm                   |

RoHS 