

TECHNICAL DATA SHEET

Part No. 156-00070
Article No. 156-00070
Type WSRFT9A



HellermannTyton's fir tree mounts provide a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. Fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold as an assembly with the cable tie.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Cable Tie	PA66HS
Material Foot Part	PA66HIRHSUV
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)

Pkg. Qty.	100
Carton Qty.	500
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Height (imperial)	.75 "
Height (metric)	19.10 mm
Length (imperial)	15.1 "
Length (metric)	383.5 mm
Max. Bundle Diameter (imperial)	4.13 "
Max. Bundle Diameter (metric)	105.0 mm
Min. Tensile Strength (imperial)	120 lbs
Min. Tensile Strength (metric)	535 N
Mounting Hole Diameter (imperial)	0.34 - 0.36 "
Mounting Hole Diameter (metric)	8.7 - 9.2 mm
Panel Thickness (imperial)	0.04 - 0.26 "
Panel Thickness (metric)	1.0 - 6.5 mm
Width (imperial)	0.5 "
Width (metric)	12.7 mm

