

TECHNICAL DATA SHEET

Part No. 156-00429
Article No. 156-00429
Type T120SHDM8



These cable tie mounts attach with a screw or bolt to an existing hole, or secure to a stud with a nut. They provide an attachment point for securing and routing a single bundle and deliver the highest level of fastening strength for critical cable security.

Material	Polyamide 4.6 (PA46)
Material Cable Tie	PA46
Material Foot Part	PA46
Operating Temperature	-40°F to +266°F (-40°C to +130°C)
Foot Part Operating Temperature	-40°F to +266°F (-40°C to +130°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Gray (GY)
Pkg. Qty.	100
Carton Qty.	1000
Customs Number	3926909988

Fixation Method	Screw Mount
Height (imperial)	0.61 "
Height (metric)	15.55 mm
Length (imperial)	8.86 "
Length (metric)	225.0 mm
Length 2 (imperial)	1.48 "
Length 2 (metric)	37.5 mm
Max. Bundle Diameter (imperial)	2.17 "
Max. Bundle Diameter (metric)	55.0 mm
Min. Tensile Strength (imperial)	120 lbs
Min. Tensile Strength (metric)	535 N
Mounting Screw Type	M8 Screw
Thickness (imperial)	0.07 "
Thickness (metric)	1.8 mm
Width (imperial)	0.30 "
Width (metric)	7.6 mm

RoHS✓