

TECHNICAL DATA SHEET

Part No. 156-00457
Article No. 156-00457
Type T50RFT7HD



HellermannTyton's fir tree mounts provide a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. Fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold as an assembly with the cable tie.

Material	Polyamide 4.6 (PA46)
Material Cable Tie	PA46
Material Foot Part	PA46
Operating Temperature	-40°F to +266°F (-40°C to +130°C)
Flammability	UL 94 V-2
UV Resistant	No
Use Conditions	For Indoor Use Only
Color	Brown (BN)
Pkg. Qty.	500
Carton Qty.	1000
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Height (imperial)	0.78 "
Height (metric)	19.8 mm
Length (imperial)	8.0 "
Length (metric)	202.0 mm
Length 2 (imperial)	0.5 "
Length 2 (metric)	11.6 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Mounting Hole Diameter (imperial)	0.24 - 0.28 "
Mounting Hole Diameter (metric)	6.2 - 7.2 mm
Panel Thickness (imperial)	0.03 - 0.28 "
Panel Thickness (metric)	0.8 - 7.0 mm
Width (imperial)	0.18 "
Width (metric)	4.6 mm

