

TECHNICAL DATA SHEET

Part No. 156-00567
Article No. 156-00567
Type T50REC23



HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.

Material	Polypropylene (PP), Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Cable Tie	PP
Material Foot Part	PA66HIRHSUV
Operating Temperature	-40°F to +185°F (-40°C to +85°C), -40°F to +230°F (-40°C to +110°C)
Flammability	UL 94 HB
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	4000
Customs Number	3926909988

Fixation Method	Edge Clip
Height (imperial)	0.05 "
Height (metric)	1.2 mm
Length (imperial)	8.0 "
Length (metric)	202.0 mm
Length 2 (imperial)	0.55 "
Length 2 (metric)	14.0 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	110 N
Panel Thickness (imperial)	0.12 - 0.24 "
Panel Thickness (metric)	3.0 - 6.0 mm
Thickness (imperial)	0.05 "
Thickness (metric)	1.2 mm
Width (imperial)	0.18 "
Width (metric)	4.6 mm

