

TECHNICAL DATA SHEET

Part No. 156-00813
Article No. 156-00813
Type T30REC4A



The cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature problems. Edge clips are widely used for fixing and bundling cables and wires within automotive, trucking, heavy equipment, solar panel, wind power, and white goods equipment manufacturing.

Material	Polyamide 6.6 heat stabilized (PA66HS), Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Cable Tie	PA66HS
Material Foot Part	PA66HIRHS
Operating Temperature	-40°F to +221°F (-40°C to +105°C), -40°F to +230°F (-40°C to +110°C)
Foot Part Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
UV Resistant	No
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	6000
Customs Number	3926909988

Fixation Method	Edge Clip
Height (imperial)	0.04 "
Height (metric)	1.1 mm
Length (imperial)	6.0 "
Length (metric)	150.0 mm
Length 2 (imperial)	0.6 "
Length 2 (metric)	14.0 mm
Max. Bundle Diameter (imperial)	1.38 "
Max. Bundle Diameter (metric)	35.0 mm
Min. Tensile Strength (imperial)	30 lbs
Min. Tensile Strength (metric)	135 N
Panel Thickness (imperial)	0.04 - 0.12 "
Panel Thickness (metric)	1.0 - 3.0 mm
Thickness (imperial)	0.04 "
Thickness (metric)	1.1 mm
Width (imperial)	0.14 "
Width (metric)	3.6 mm

RoHS