

# TECHNICAL DATA SHEET

**Part No.** 156-00877  
**Article No.** 156-00877  
**Type** T50ROSEC23



HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.

<b>Material</b>	Polyamide 6.6 heat stabilized (PA66HS), Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
<b>Material Cable Tie</b>	PA66HS
<b>Material Foot Part</b>	PA66HIRHS
<b>Operating Temperature</b>	-40°F to +221°F (-40°C to +105°C)
<b>Foot Part Operating Temperature</b>	-40°F to +221°F (-40°C to +105°C)
<b>Flammability</b>	UL 94 HB
<b>UV Resistant</b>	No
<b>Use Conditions</b>	For Indoor and Outdoor Use
<b>Color</b>	Black (BK)
<b>Pkg. Qty.</b>	500
<b>Carton Qty.</b>	4000
<b>Customs Number</b>	3926909988

<b>Fixation Method</b>	Edge Clip
<b>Height (imperial)</b>	0.05 "
<b>Height (metric)</b>	1.3 mm
<b>Length (imperial)</b>	8.0 "
<b>Length (metric)</b>	200.0 mm
<b>Length 2 (imperial)</b>	0.55 "
<b>Length 2 (metric)</b>	14.8 mm
<b>Max. Bundle Diameter (imperial)</b>	1.97 "
<b>Max. Bundle Diameter (metric)</b>	50.0 mm
<b>Min. Tensile Strength (imperial)</b>	50 lbs
<b>Min. Tensile Strength (metric)</b>	225 N
<b>Panel Thickness (imperial)</b>	0.12 - 0.24 "
<b>Panel Thickness (metric)</b>	3.0 - 6.0 mm
<b>Thickness (imperial)</b>	0.05 "
<b>Thickness (metric)</b>	1.3 mm
<b>Width (imperial)</b>	0.18 "
<b>Width (metric)</b>	4.6 mm

