

# TECHNICAL DATA SHEET

**Part No.** 156-00947  
**Article No.** 156-00947  
**Type** T30REC19



HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge slip in place.

|                              |                                                                                                                |
|------------------------------|----------------------------------------------------------------------------------------------------------------|
| <b>Material</b>              | Polyamide 6.6 heat stabilized (PA66HS),<br>Polyamide 6.6, high impact modified, heat<br>stabilized (PA66HIRHS) |
| <b>Material Cable Tie</b>    | PA66HS                                                                                                         |
| <b>Material Foot Part</b>    | PA66HIRHS                                                                                                      |
| <b>Operating Temperature</b> | -40°F to +185°F (-40°C to +85°C), -40°F to<br>+230°F (-40°C to +110°C)                                         |
| <b>UV Resistant</b>          | No                                                                                                             |
| <b>Use Conditions</b>        | For Indoor and Outdoor Use                                                                                     |
| <b>Color</b>                 | Black (BK)                                                                                                     |
| <b>Pkg. Qty.</b>             | 500                                                                                                            |
| <b>Carton Qty.</b>           | 4000                                                                                                           |
| <b>Customs Number</b>        | 3926909988                                                                                                     |

|                                         |               |
|-----------------------------------------|---------------|
| <b>Fixation Method</b>                  | Edge Clip     |
| <b>Height (imperial)</b>                | 0.55 "        |
| <b>Height (metric)</b>                  | 1.1 mm        |
| <b>Length (imperial)</b>                | 6.0 "         |
| <b>Length (metric)</b>                  | 148.0 mm      |
| <b>Length 2 (imperial)</b>              | 0.6 "         |
| <b>Length 2 (metric)</b>                | 14.8 mm       |
| <b>Max. Bundle Diameter (imperial)</b>  | 1.38 "        |
| <b>Max. Bundle Diameter (metric)</b>    | 35.0 mm       |
| <b>Min. Tensile Strength (imperial)</b> | 30 lbs        |
| <b>Min. Tensile Strength (metric)</b>   | 135 N         |
| <b>Panel Thickness (imperial)</b>       | 0.12 - 0.24 " |
| <b>Panel Thickness (metric)</b>         | 3.0 - 6.0 mm  |
| <b>Thickness (imperial)</b>             | 0.04 "        |
| <b>Width (imperial)</b>                 | 0.14 "        |
| <b>Width (metric)</b>                   | 3.6 mm        |

RoHS