

TECHNICAL DATA SHEET

Part No. 156-01092
Article No. 156-01092
Type T50RLOC10-14-SET



HellermannTyton's two-piece cable tie assembly offers dual bundle routing. The clip portion creates a full and secure lock completely around one bundle, while the cable tie creates a secure solution for a second bundle.

Material	Polyamide 6.6 heat stabilized (PA66HS), Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	3000
Carton Qty.	3000
Customs Number	3926909988

Height (imperial)	1.08 "
Height (metric)	27.4 mm
Length (imperial)	1.09 "
Length (metric)	27.6 mm
Max. Bundle Diameter (imperial)	0.55 "
Max. Bundle Diameter (metric)	14.0 mm
Min. Bundle Diameter (imperial)	0.39 "
Min. Bundle Diameter (metric)	10.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Nominal Bundle Diameter (imperial)	0.39 " - 0.55 "
Nominal Bundle Diameter (metric)	10.0 mm - 14.0 mm
Width (imperial)	0.47 "
Width (metric)	12.0 mm

