

TECHNICAL DATA SHEET

Part No. 156-01093
Article No. 156-01093
Type T50RLOC10-14



HellermannTyton's two-piece cable tie assembly offers dual bundle routing. The omega clip portion creates a full and secure lock completely around one bundle, while the cable tie creates a secure solution for a second bundle.

Material	Polyamide 6.6 heat stabilized (PA66HS), Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	500
Carton Qty.	2500
Customs Number	3926909988

Height (imperial)	1.72 "
Height (metric)	43.75 mm
Length (imperial)	1.72 "
Length (metric)	43.73 mm
Length 2 (imperial)	2.5 "
Length 2 (metric)	63.6 mm
Max. Bundle Diameter (imperial)	0.55 "
Max. Bundle Diameter (metric)	14.0 mm
Min. Bundle Diameter (imperial)	0.39 "
Min. Bundle Diameter (metric)	10.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	220 N
Nominal Bundle Diameter (imperial)	0.39 - 0.55 "
Nominal Bundle Diameter (metric)	10.0 mm - 14.0 mm
Width (imperial)	0.47 "
Width (metric)	12.0 mm

