

TECHNICAL DATA SHEET

Part No. 156-01289
Article No. 156-01289
Type T50RLOC5-9-SET



The Locking Clip creates a full and secure lock completely around a wire bundle ranging from 10-14mm. The fixating fir tree on this clip allows for the clip to be secured into a panel by a 6mm round hole.

Material	Polyamide 6.6 heat stabilized (PA66HS), Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)

Pkg. Qty.	1000
Carton Qty.	1000
Customs Number	3926909988

Height (imperial)	0.93 "
Height (metric)	23.6 mm
Length (imperial)	0.93 "
Length (metric)	23.7 mm
Max. Bundle Diameter (imperial)	0.35 "
Max. Bundle Diameter (metric)	9.0 mm
Min. Bundle Diameter (imperial)	0.2 "
Min. Bundle Diameter (metric)	5.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Nominal Bundle Diameter (imperial)	0.20 " - 0.35 "
Nominal Bundle Diameter (metric)	5.0 mm - 9.0 mm
Width (imperial)	0.47 "
Width (metric)	12.0 mm

