

TECHNICAL DATA SHEET

Part No. 156-01295
Article No. 156-01295
Type T50R0SBS6USET



Oval Shaped Stud Mount's special design allows for a 0.2" (5.5mm) lateral adjustment, allowing for any misalignment of the stud or incorrect position of the tie on the cables. The "soft push" mount allows it to be installed onto a weld stud without the use of any tools.

Material	Polyamide 6.6 heat stabilized (PA66HS), Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Cable Tie	PA66HS
Material Foot Part	PA66HIRHSUV
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)

Pkg. Qty.	2000
Carton Qty.	2000
Customs Number	3926909988

Fixation Method	Stud Mount
Height (imperial)	0.87 "
Height (metric)	21.5 mm
Length (imperial)	8.0 "
Length (metric)	203.2 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	25 lbs
Min. Tensile Strength (metric)	110 N
Stud Diameter (metric)	M6
Width (imperial)	0.55 "

