

TECHNICAL DATA SHEET

Part No. 156-01561
Article No. 156-01561
Type T120ROSFT9CLG



HellermannTyton Heavy Duty Fir Tree Mounts are designed with extreme applications in mind. They are optimized for up to 3-to-1 extraction versus insertion force to make assembly fast and easy. These mounts are sold as an assembly with a cable tie.

Material	Polyamide 6.6 heat stabilized (PA66HS), Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Cable Tie	PA66HS
Material Foot Part	PA66HIRHSUV
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	100
Carton Qty.	500
Customs Number	3926909988

Fixation Method	Fir tree for round holes
Height (imperial)	1.16 "
Height (metric)	29.6 mm
Length (imperial)	15.0 "
Length (metric)	385.0 mm
Max. Bundle Diameter (imperial)	4.13 "
Max. Bundle Diameter (metric)	105.0 mm
Min. Tensile Strength (imperial)	120 lbs
Min. Tensile Strength (metric)	535 N
Mounting Hole Diameter (imperial)	0.34 - 0.36 "
Mounting Hole Diameter (metric)	8.75 - 9.25 mm
Panel Thickness (imperial)	0.09 - 0.50 "
Panel Thickness (metric)	1.0 - 12.7 mm
Thickness (imperial)	0.07 "
Thickness (metric)	1.8 mm
Width (imperial)	0.30 "
Width (metric)	7.6 mm

