

TECHNICAL DATA SHEET

Part No. 156-01572
Article No. 156-01572
Type T50R0SBS5UM90SET



Oval shaped stud mount's special design allows for a 0.2" (5.5mm) lateral adjustment in case of misalignment of the stud or incorrect position of the tie on the cables. The "soft push" mount allows it to be installed onto a weld stud without the use of any tools.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV), Polyacetal (POM)
Material Cable Tie	PA66HIRHSUV
Material Foot Part	POM
Operating Temperature	-40°F to +221°F (-40°C to +105°C), -22°F to +194°F (-30°C to +90°C)
Operating Temperature, 500h	+329°F (+165°C)
Operating Temperature, 1000h	+320°F (+160°C)
Operating Temperature, 5000h	+257°F (+125°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK), Dark Gray (DKGY)
Pkg. Qty.	2000
Carton Qty.	2000 EA
Customs Number	3926909988

Fixation Method	Stud Mount
Height (imperial)	0.98 "
Height (metric)	25.0 mm
Length (imperial)	7.95 "
Length (metric)	202.0 mm
Max. Bundle Diameter (imperial)	1.97 "
Max. Bundle Diameter (metric)	50.0 mm
Min. Tensile Strength (imperial)	50 lbs
Min. Tensile Strength (metric)	225 N
Stud Diameter (metric)	5.0 mm
Width (imperial)	0.46 "
Width (metric)	11.72 mm

