

TECHNICAL DATA SHEET

Part No. 156-01614
Article No. 156-01614
Type MOC8FLOC20-25



The MOC to MOC is a rotatable dual routing clip that keeps two routings secured and separated. A swivel coupler allows them to rotate independently of each other.

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant	Yes
Use Conditions	For Indoor and Outdoor Use
Color	Black (BK)
Pkg. Qty.	1000
Carton Qty.	1000
Customs Number	3926909988

Height (imperial)	1.53 "
Height (metric)	38.9 mm
Length (imperial)	2.06 "
Length (metric)	52.4 mm
Length 2 (imperial)	1.16 "
Length 2 (metric)	29.7 mm
Max. Bundle Diameter (imperial)	0.98 "
Max. Bundle Diameter (metric)	25.0 mm
Max. Bundle Diameter 2 (imperial)	0.35 "
Max. Bundle Diameter 2 (metric)	9.0 mm
Min. Bundle Diameter (imperial)	0.79 "
Min. Bundle Diameter (metric)	20.0 mm
Min. Bundle Diameter 2 (imperial)	0.28 "
Min. Bundle Diameter 2 (metric)	7.0 mm
Width (imperial)	0.47 "
Width (metric)	12.00 mm

HF ✓

RoHS ✓